

DIGITAL USER GUIDE

Reveal. Inspect. Verify.

100-LED 18W UV flashlight torch for stain, document and inspection work



395 nm

100 UV LEDs
18W class

AA alkaline
6×AA

No lumen figure

Two pack options

Owner locks: wavelength **395 nm** · **AA alkaline** primary cells · **no lumen** figure · one product for both pack options (Without Battery / With Battery).

Your exact product

SKUs: **1x18w-UV** · **1x18w-UV-6BTRY**
Brand **amiciVision** · Product ID **8360593326235**
Version 1.0 · 19 September 2026

Find the help you need

Tap a section. PDF bookmarks match these entries.

Safety and scope	3
What's in the box & batteries	4
Operation	5
Specifications	6
Care, troubleshooting, support	7
Sources and limits	8

Safety and scope

UV light needs basic eye/skin care. No invented certifications.

UV precautions

Do not stare into the beam. Avoid prolonged skin exposure at close range. Not a toy. No formal UV safety certification is published on the listing — do not invent one.

Battery chemistry

Owner: **AA alkaline** primary cells. Do not read listing “per charge” wording as a rechargeable-pack claim. Do not mix old/new or alkaline/NiMH cells in one set.

Model scope

One digital manual covers both Shopify options: Without Battery (1x18w-UV) and With Battery (1x18w-UV-6BTRY). Same UV head.

What's in the box & batteries

Pack contents depend on the option you ordered.

Without Battery (1x18w-UV)

UV flashlight torch (aluminium body, 100 UV LEDs / 18W class). AA cells not included — use 6×AA alkaline.

With Battery (1x18w-UV-6BTRY)

Same torch plus **6×AA alkaline** included for immediate use.

Install cells

1. Open the battery compartment per end-cap / body markings.
2. Insert 6×AA alkaline with correct polarity.
3. Close firmly. Do not force damaged threads.

Live Shopify option title may still say “Size” — recommend rename to Battery later (not mutated in this publish).

Operation

Use in a dim area for inspection tasks listed on the product page.

Typical uses (listing)

Document / currency checks, stain detection, HVAC leak tracing aids, and similar UV inspection tasks. Follow switch markings. Avoid aiming at eyes.

Working distance (listing marketing)

Up to about **15 ft / 4.5 m** — a marketing reach claim, not a lab lumen chart.

Runtime (listing marketing)

Up to about **4 hours** continuous UV use on a set of 6×AA alkaline cells. Replace the full set when output weakens. Alkaline primary-cell runtime — not a rechargeable “per charge” claim.

Specifications

Only published / owner-confirmed figures.

Item	Value	Basis
SKUs	1x18w-UV · 1x18w-UV-6BTRY	Shopify
Brand (handle)	amiciVision	Handle
LEDs / power class	100 UV LEDs · 18W	Listing
Wavelength	395 nm	Owner
Lumens	Not published — do not invent	Owner
Power source	6×AA alkaline	Owner
Runtime claim	~4 h continuous / alkaline set	Listing marketing
Reach claim	~15 ft / 4.5 m	Listing marketing
Body	Aircraft-grade aluminium (listing)	Listing
Source PDF	None — listing + owner	Evidence

Care, troubleshooting, support

Keep it simple — no invented IP ratings.

Observation	Next step
Beam weak / off	Replace all 6 alkaline cells; check polarity and end-cap contact.
Flicker	Reseat cells; clean contacts; replace the full set.
Moisture on body	Wipe dry. No IP rating published — do not immerse.
Need returns help	Listing emphasises 30-day returns; contact support for your order.

[Contact amiciKart support](#)

[Open product page](#)

Sources and limits

v1.0 publish of the listing-based draft (was v0.1).

Version note

Draft v0.1 (18 Sep 2026) was owner-review only. This **v1.0** removes draft watermarks and is the publish candidate for SharePoint New Manuals + Shopify Download manual.

Evidence

Live listing product.js · owner corrections 18 Sep 2026 IST (395 nm, AA alkaline, no lumen) · draft ledger.

Unresolved

No supplier PDF · no lumen · no formal UV certification on listing · physical switch labeling from listing photos only.